

MICROHARDNESS TESTER

(ALPHA-MHT-2000Z)


ALPHA-MHT-2000Z is an auto turret precision Micro Vickers hardness testing instrument for Vickers and Knoop indenters (Part No. ALPHA MHT-2000Z). Features include variable testing forces (10, 25, 50, 100, 200, 300, 500, 1000 and 2000 gram load), 10X and 40X objectives, a large LCD screen for displaying measuring methods, testing force, indentation length, hardness value, dwell time and the number of measurements. The ALPHA- MHT-2000Z can save and export data to either a printer or a PC via a RS232 interface cable.

- Vickers or Knoop
- Auto-turret
- Built-in printer
- Load range 10-2000 grams
- Scales (HV, HK)
- Dwell time 5-60 seconds
- Auto hardness conversion to other scales (HRA, HRB, HRC, HV, HK, HBW, etc)
- Long lasting Halogen lamp
- Easy to use
- LCD speed display
- User friendly
- Robust and durable design
- Easy to service

Technical Specifications:

Feature	ALPHA-MHT-2000Z
Indenter types	Vickers or Knoop
Objectives	10X and 40X
Indenter positioning	Auto turret
Testing Force (gf)	10,25,50,100,200,300,400,500,1000,2000
Indenter measurement	Digital
Auto Hardness Conversion	HRA, HRG, HRK, HRB, HRC, HV, HK, HBW, etc
Testing Range	1 HV ~ 3000 HV
X-Y Anvil Size	4 x 4-inch (100 x 100 mm)
X-Y Anvil Travel	5 x 1-inch (125 x 25 mm)
Maximum Height of Specimen	2.8-inch (70 mm)
Dwell Time	5-60 seconds
Illumination	Halogen
Dimensions (W x D x H)	17 x 19 x 17-inch (425 x 490 x 425mm)
Electrical Specifications	110V / 220V 50/60 Hz
Weight	88 lbs (40 kg)
Part No.	ALPHA -MHT-2000Z

PACE Technologies
 3601 E. 34th St, Tucson, AZ 85713 USA
 Phone +1 520-882-6598 FAX +1 520-882-6599
 www.metallographic.com
 email pace@metallographic.com




Microhardness Tester Accessories:

Description	Part Number
Vickers indenter	823-401
Knoop indenter	823-411
10X eyepiece	823-341
10X Objective	823-311
40X Objective	823-331
X-Y anvil	823-701
Dust cover	823-902
Sample leveler (optional)	823-741
Digital camera (optional)	MD50-T
Camera adapter (optional)	823-361
Microhardness indentation measurement software (optional)	Microhardness Pro

MICROHARDNESS PRO Software


• Microhardness Pro 4.2 is an easy to use image analysis software for measuring microhardness and for generating easy to distribute Excel reports. It is a single screen Windows based system.

• The Microhardness Pro 4.2 software can handle both gray monochrome (8 bit) and color (24 bit) images. Multiple images of any size can be opened and displayed on the screen for analysis or comparison. The software supports the most common formats like BMP, JPEG, TIFF, PNG, GIF and PSD. Live images also can be observed and captured on the same platform. Since the system is in a Windows environment, graphs and charts displayed on the monitor can be quickly transferred into other Windows based programs such as, MS Word, MS Excel or any other commercial Windows based software for the purpose producing reports and presentations.



PACE[®]
TECHNOLOGIES
www.metallographic.com


PACE Technologies
 3601 E. 34th St
 Tucson, AZ 85713 USA
 Phone +1 520-882-6598
 FAX +1 520-882-6599
www.metallographic.com
 email pace@metallographic.com



Sample Leveling Fixture



C-mount Camera Adapter



Hardness Test Blocks



Machinery directive 2006/42/EC
 Low Voltage Directive 2006/95/EC
 Electromagnetic Compatibility directive 2004/108/EC